Technical Product Data Sheet

MICROFOCUS X-RAY TUBES

PRODUCT LINE CT PLUS







Product image




Microfocus X-ray tube XWT-300-CT Plus



XWT-300-CT Plus with new collimator



XWT-300-CT Plus with new cooling circuit



JIMA resolution 4.0 µm: 225kV - 300kV tubes

Technical data

Data	Product line CT Plus						
Max. voltage (kV)	225	240	300				
Min. voltage (kV)	20	20 20					
Max. current (mA)	3.0	3.0	3.0				
Min. current (mA)	0.05	0.05	0.05				
Max. power, emission (Watt)	500	500	500				
Max. power, target (Watt)	450	450	450				
JIMA resolution (µm)	4.0	4.0	4.0				
Tube type	Reflection						
Target type	High Power						
Target material	Tungsten						
Min. focus-object- distance (FOD, mm)	8.0	8.0	8.0				
Opening angle (approx. °)	40	40	40				
Mounting length incl. 90° HV plug (mm)	790	881	916				
Tube weight (approx. kg)	50	50	69				

Highlights

- Paramount tube power 500 Watt also at maximum voltage of 300 kV
- Internal cooling of the tube head and turbo pump for highest stability of focal spot position increases accuracy of CT scans
- Reduced heel effect and round focal spot by redesigned reflection target
- Automatic Intensity Control (AIC) for continuous intensity of radiation
- Unlimited lifetime

See our new catalogue **Options and Accessories** to find additional auxiliary equipment for your X-RAY WorX tube.

Scope of delivery

- Open microfocus X-ray tube with reflection target, turbo vacuum pump, vacuum gauge, and electronic drive unit
- Internal liquid cooling of the tube head, target and turbo pump
- High voltage generator and high voltage cable
- Prevacuum pump with vacuum hose
- Peltier-type cooler with hoses and cooling agent
- ► Tube controller, power supplies, and safety relays on 19" mounting panels
- Collimator with filter holder (including Al, Sn, and Cu filters of different thicknesses)
- Set of cables for electrical connection of X-ray tube and components
- Spare parts case, documentation, operating software




Product Line CT Plus


Focal spot size

		Voltage [kV]							
		60	100	150	190	225	240	300	
Target power [W]	50	60	60	60	55	40	40	40	
	100	110	105	100	85	80	75	75	
	150	140	175	145	125	125	125	125	
	200		250	190	170	170	170	170	
	250		340	235	235	225	225	225	
	300			300	300	285	285	285	
	350			370	370	340	340	340	
	400			450	450	400	400	400	
	450				500	450	450	400	

Focal spot sizes in microns (μm) based on measurements according to EN 12543-5.



Tube dimensions



X-RAY WorX GmbH • Siemensstrasse 26 • D-30827 Garbsen • Germany
Tel: +49 5131 48712-60 • Fax: +49 5131 48712-66 • info@x-ray-worx.com • www.x-ray-worx.com